

Esempi audio Vertigo Sound VSC-2

Esempi audio Vertigo Sound VSC 2, impostazioni

Vocal 2 VCS 1: Soft, Attack .1, Release .9, Gain Reduction 4 dB, Sidechain Filter 90 Hz, un solo compressore

Vocal 2 VCS 2: primo compressore come Vocal 2 VCS 1, seguito da secondo compressore con Ratio 8, Attack 10, Release .3, Sidechain Filter Off, Gain Out 0 dB

RHG_80_D_LP01 VCS 2: Soft, Attack .01, Releases .3, Sidechain Filter 90 Hz, Gain Reduction 6 db

RHG_80_D_LP02 VCS 2: Ratio 8, Attack .3, Release .3, Sidechain Filter 60 Hz, Gain Reduction 12 dB

RHG_80_D_LP03 VSC2: Soft, Attack 30, Release 3, Sidechain Filter 90 Hz, Gain reduction 3 dB, seguito da secondo compressore con Ratio 8, Attack .01, Release .9, Sidechain Filter 60 Hz, Gain Reduction 3 db gr

Esempio 5 VSC 2: Soft, Attack 10, Release .3, Gain Reduction 3 dB

Esempio 4 VSC 2: Ratio 8, Attack .3, Release .3, quasi al massimo il gain out

Esempio 2 VSC 2: Soft, Attack 1, Release .6, Sidechain filter Off, Gain Reduction 4 dB

Esempio 1a VSC 2: Brick, Attack 3, Release .6

Esempio 1 VSC 2: Ratio 2, Attack 3, Release .6, Sidechain Filter 90 Hz, Gain Reduction 4 dB